

**NIBCO**

1516 Middlebury Street

Elkhart, IN 46516-4740

Phone: 574.295.3000 • **Fax:** 800.234.0557**Email:** info@nibco.com • **Web site:** www.nibco.com**T-585-70-W3 - Two-Piece Bronze Ball Valve - Full Port, Three-Way, Threaded**

The NIBCO® bronze ball valve provides ease of operation with quarter-turn (90 degrees) open to close. The reinforced PTFE seating ring and brass hard chrome plated ball exhibit high chemical resistance properties and is recommended for many high pressure applications. The two-piece valve features thread ends for easy installation. Please refer to NIBCO technical data sheet, valve selection guides and catalog for engineering and installation information. Choose NIBCO® ball valves for the most

+ n



Material Number	UPC Code	Valve Size	Operation Type	Description
NL95L06	039923797483	1/2 in	CS Standard Lever Handle	T58570W3 1/2 3 WAY BALL VALVE
NL95L08	039923797490	3/4 in	CS Standard Lever Handle	T58570W3 3/4 3 WAY BALL VALVE
NL95L0A	039923797506	1 in	CS Standard Lever Handle	T58570W3 1" 3 WAY BALL VALVE