

**NIBCO**

1516 Middlebury Street

Elkhart, IN 46516-4740

Phone: 574.295.3000 • **Fax:** 800.234.0557**Email:** info@nibco.com • **Web site:** www.nibco.com**S-585-70 - Two-Piece Bronze Ball Valve - Full Port, Solder End Connections**

The NIBCO® bronze ball valve provides ease of operation with quarter-turn (90 degrees) open to close. The two-piece valve is ideal for commercial and light industrial process applications that may include HVAC, hot and cold domestic water, low pressure steam, compressed air, LP gas and natural gas. Please refer to NIBCO technical data sheet, valve selection guides and catalog engineering and installation information. Choose NIBCO® ball valves for the most specified, versatile and economical

+ n



1 2 3

Material Number	UPC Code	Connection Type	Valve Size	Valve Operator	Description
<u>NJ83058</u>	039923692368	S -- Female Solder Cup	3/4	CS Wing Handle	S58570W 3/4 W/WING HDL
<u>NJ830A8</u>	039923680358	S -- Female Solder Cup	3/4	SS Standard Lever Handle	S58570SSHN 3/4 W/SS HDL & NUT
<u>NJ830E6</u>	039923678690	S -- Female Solder Cup	1/2	CS Extended Lever Handle	S58570EL 1/2 W/E x T LEVER HDLE
<u>NJ830E8</u>	039923678706	S -- Female Solder Cup	3/4	CS Extended Lever Handle	S58570EL 3/4 W/E x T LEVER HDLE
<u>NJ830EA</u>	039923678713	S -- Female Solder Cup	1	CS Extended Lever Handle	S58570EL 1 W/E x T LEVER HDLE
<u>NJ830L4</u>	039923679758	S -- Female Solder Cup	1/4	CS Locking Lever Handle	S58570LL 1/4 W/LOCK HDL
<u>NJ830L5</u>	039923679765	S -- Female Solder Cup	3/8	CS Locking Lever Handle	S58570LL 3/8 W/LOCK HDL

Material Number	UPC Code	Connection Type	Valve Size	Valve Operator	Description
<u>NJ830L6</u>	039923679772	S -- Female Solder Cup	1/2	CS Locking Lever Handle	S58570LL 1/2 W/LOCK HDL
<u>NJ830L8</u>	039923679789	S -- Female Solder Cup	3/4	CS Locking Lever Handle	S58570LL 3/4 W/LOCK HDL
<u>NJ830LA</u>	039923679796	S -- Female Solder Cup	1	CS Locking Lever Handle	S58570LL 1 W/LOCK HDL
<u>NJ830Q8</u>	039923679062	S -- Female Solder Cup	3/4	CS Extended Lever Handle with Memory Stop	S58570ELM 3/4 W/E x T LEV MEM STOP HDL
<u>NJ831EB</u>	039923678720	S -- Female Solder Cup	1 1/4	CS Extended Lever Handle	S58570EL 1-1/4 W/E x T LEVER HANDLE
<u>NJ831EC</u>	039923678737	S -- Female Solder Cup	1 1/2	CS Extended Lever Handle	S58570EL 1-1/2 W/E x T LEVER HANDLE
<u>NJ831ED</u>	039923678744	S -- Female Solder Cup	2	CS Extended Lever Handle	S58570EL 2 W/E x T LEV HANDLE
<u>NJ831LB</u>	039923679802	S -- Female Solder Cup	1 1/4	CS Locking Lever Handle	S58570LL 1-1/4 W/LOCK HDL
<u>NJ831LC</u>	039923679819	S -- Female Solder Cup	1 1/2	CS Locking Lever Handle	S58570LL 1-1/2 W/LOCK HDL
<u>NJ831LD</u>	039923679826	S -- Female Solder Cup	2	CS Locking Lever Handle	S58570LL 2 W/LOCK HDL
<u>NJ832QB</u>	039923679086	S -- Female Solder Cup	1 1/4	CS Extended Lever Handle with Memory Stop	S58570ELM 1-1/4 W/E x T LEV MEM STOP HDL
<u>NJ8330B</u>	039923678904	S -- Female Solder Cup	1 1/4	CS Standard Lever Handle with Memory Stop	S58570M 1-1/4 W/MEM STOP HDLE
<u>NJ8330C</u>	039923678911	S -- Female Solder Cup	1 1/2	CS Standard Lever Handle with Memory Stop	S58570M 1-1/2 W/MEM STOP HDLE
<u>NJ8330D</u>	039923678928	S -- Female Solder Cup	2	CS Standard Lever Handle with Memory Stop	S58570M 2 W/MEM STOP HDLE
<u>NJ83I04</u>	039923678850	S -- Female Solder Cup	1/4	CS Standard Lever Handle with Memory Stop	S58570M 1/4 W/MEM STOP HDL

Material Number	UPC Code	Connection Type	Valve Size	Valve Operator	Description
<u>NJ83I05</u>	039923678867	S -- Female Solder Cup	3/8	CS Standard Lever Handle with Memory Stop	S58570M 3/8 W/MEM STOP HDL
<u>NJ83I06</u>	039923678874	S -- Female Solder Cup	1/2	CS Standard Lever Handle with Memory Stop	S58570M 1/2 W/MEM ST HDLE
<u>NJ83I08</u>	039923678881	S -- Female Solder Cup	3/4	CS Standard Lever Handle with Memory Stop	S58570M 3/4 W/MEM STOP HDLE