

Lead-Free* Bronze Stop & Drain Valves

Silicon Performance Bronze™ Alloy •


NSF/ANSI 61-8 (includes Annex F and G) and NSF/ANSI 372

Pressure Rating: 125 PSI Non-Shock Cold Working Pressure

Maximum Pressure / Temperature: 125 PSI at 180° F

Lead-Free* markings:

Double oval in body casting and white handle



MATERIALS LIST


PART	SPECIFICATION
Body	ASTM B584 Alloy C87850
Bonnet	ASTM B584 Alloy C87850
Stem	Cold-formed Copper Alloy
Seat Disc	EPDM
Seat Disc Screw	Stainless Steel, Type 410
Packing Nut	Free Cutting Brass - ASTM B16
Packing	Graphite Impregnated, Asbestos-Free
Handwheel	Epoxy Coated Zinc Alloy
Handwheel Screw	Carbon Steel - Clear Chromate Finish



726-LF
Cup x Cup




76-LF
FIP x FIP



76-LF

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		A	B	
Stop & Waste Valve	1/2"	2 ³ / ₁₆ "	2 ⁹ / ₁₆ "	.54 lb
FIP x FIP	3/4"	2 ⁵ / ₁₆ "	2 ⁹ / ₁₆ "	.60 lb



726-LF

DESCRIPTION	*NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve	1/2"	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.42 lb
Cup x Cup	3/4"	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.49 lb

*Weighted average lead content ≤ 0.25%